

FLOOR ANCHOR SYSTEMS

TESTED AND CERTIFIED FOR USE WITH Q'STRAINT® & SURE-LOK® SYSTEMS

NOW YOU CAN MIX & MATCH RETRACTORS & MANUAL BELTS FROM Q'STRAINT & SURE-LOK BY USING OMNI FLOOR ANCHOR SYSTEMS*





SURE-L&K

Safe and Secure

OMNI FLOOR ANCHORAGES

FOR BOTH Q'STRAINT AND SURE-LOK PRODUCTS

All OMNI Floor Anchor Systems feature stainless steel or aluminum materials designed for demanding transportation environments. It has always been recommended that tie-downs match with the brand of their floor anchorages. Now with the OMNI series you can reduce your liability and know that your products are tested and certified for both Q'Straint and Sure-Lok systems.

Designed for agencies that require total flexibility in a mixed-brand environment, the OMNI line takes the guess work out of securing your passengers.



FE753NA100-04-3 Flange Series L-Track Pre-Drilled

- 100" (254cm) in length
- Standard 82 degree countersunk holes are pre-drilled every 4" (102mm)
- Accommodates 5/16" (8mm) bolts



Regular Series L-Track Pre-Drilled

- 100" (254cm) in length
- Standard 82 degree countersunk holes are pre-drilled every 4" (102mm)
- Accommodates 5/16" (8mm) bolts



FE752NA100-04-3 Surface Angled Series L-Track Pre-Drilled

- 100" (254cm) in length
- Standard 82 degree countersunk holes are pre-drilled every 4" (102mm)
- Accommodates 5/16" (8mm) bolts



q5-7570-A Recessed L-Pocket with Cover



FE201163 Flush Mount L-Pocket



Q5-7571-A Oval L-Pocket

KIT INCLUDES:

- L-Track Floor Pocket with Cover
- (2) 5/16" (8mm) Bolts 1.5" (38mm) in length
- Washer and (2) Hex Nuts



- L-Track Floor Plate
- 7/16" (11mm) Bolt 3.5" (89mm) in length
- Washer and Hex Nut



- L-Track Floor Pocket
- 3/8" (9.5mm) Bolt 2.5" (63.5mm) in length
- Washer and Hex Nut



08-7580-A Slide 'N Click Floor Anchor

KIT INCLUDES:

- Bottom Assembly
- 3/8" (9.5mm) Bolt 2.5" (63.5mm) in length
- Washer, Hex Nut and Blue Plug



05-8525-sc2 Slide 'N Click Stowage Bracket

Bracket has passed the vibration and crash test and is designed to be mounted on the vehicle interior walls

Holds (2) Slide 'N Click Retractors



Q5-8525-sc Slide 'N Click Stowage Bracket

Bracket has passed the vibration and crash test and is designed to be mounted on the vehicle interior walls

Holds (4) Slide 'N Click Retractors



L-TRACK

All OMNI Approved L-Track features a new profile designed to be compatible with all Q'Straint and Sure-Lok tie-downs and occupant restraints. Aluminum L-Track is the most widely used floor anchorage in the transportation industry, offering superior strength and corrosion resistance. Installing L-Track provides maximum flexibility to accommodate many different wheelchair positions. OMNI L-Track is an aluminum alloy (6061-T6) and can be configured in custom lengths, anodized finishes and drill patterns, please contact us for details.

L-POCKETS

RECESSED L-POCKET WITH COVER

The OMNI covered stainless steel floor pocket ensures your L-Track stays free of debris when not in use. Its recessed design works with most typical floor applications of 1/2" (13mm) and installs quickly with two bolts. An integrated magnet securely holds the hinged cover in the closed position.



The OMNI flush pocket offers the first ever recessed L-Track pocket with a single bolt design. Designed to recess only 3/8" (9.5mm) the pocket is ideal for modern floors featuring composite materials. The stainless steel casting also features sweeping guides on each side, to allow for easy removal of debris.

OVAL L-POCKET

The sleek design minimizes tripping and interference with wheelchair casters, while its high quality stainless steel prevents corrosion even in the harshest of transit environments. Side L-Track fitting guides help to prevent operator error by keeping your tie-down fittings centered and secured. OMNI's oval floor pocket also offers simple installation using just a single bolt. The surface mount design makes it unnecessary to modify flooring surfaces.





SLIDE 'N CLICK®

This popular and patented anchorage is now an OMNI approved product! Slide 'N Click's 360 degree design eliminates any need for alignment and makes it virtually foolproof for the operator. Whether you use a Q'Straint QRT MAX, Deluxe or the Sure-Lok Titan Series, one hand is all that is needed to attach or remove your tie-downs thanks to the easy-to-use positive locking plunger.

ADDITIONAL ACCESSORIES



FE201006 5/16" (8mm) Track Bolts

Bolts are 3" (76.2mm) long with automotive grade plating and a special sealant is applied under the bolt head to provide a seal between the track and the bolt.

KIT INCLUDES:

• (100) bolts, washers and lock nuts



End Cap for Flange Series L-Track

These L-Track End Caps finish off your flush-mount flange series installation for a professional look.

They feature a tapered edge to minimize snags and catches on the track edge.



eco6059
End Cap
for Surface
Angled
Series
L-Track

With surface mount L-Track, protective end caps allow for a gradual rise at the ends of the track.

The caps reduce the risk of tripping and are less of an obstacle for wheelchairs and other mobility devices.



*WARNING: Using OMNI anchorages and track make it possible to use both Q'Straint and Sure-Lok tiedowns. Every retractor in a wheelchair position must be EITHER from Q'Straint or Sure-Lok -- never mix brands on a four-point securement. OMNI anchorages are strictly tested and certified to be used with approved Q'Straint and Sure-Lok systems. Other non-approved systems should not be used with OMNI anchorages at any time.

All OMNI Floor Anchor Systems have been tested and meet the following standards and their applicable sections when used with a complete Q'Straint or Sure-Lok System:

- Americans with Disabilities Act (ADA) "Accessibility Specifications for Transportation Vehicles"
- Applicable NHTSA Federal Motor Vehicles Safety Standards
- RESNA Vol. 4, Sec.18 Formerly SAEJ2249 Recommended Practice –
 Wheelchair Tie-down and Occupant Restraint Systems for use in Motor Vehicles
- ISO 10542 Technical Systems and Aids for Disabled or Handicapped Persons -Wheelchair Tie-down and Occupant Restraint Systems
- Canadian Standard Association (CSA) -"Mobility Aid and Occupant Restraint (MASOR) systems"

Q'Straint USA: 5553 Ravenswood Road, #110 • Ft. Lauderdale, FL 33312 • Tel: (800) 987-9987 • Fax: (954) 986-0021 **Q'Straint Canada:** 18-100 Sheldon Dr. • Cambridge, ON N1R 7S7 • Tel: (800) 987-9987

Qstraint.com

2501 Baglyos Circle • Bethlehem, PA 18020-8027 • Tel: (866) 787-3565 • Fax: (866) 843-3696

Sure-Lok.com



